

LightPath 354996 | 3mm Dia., 0.30 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock #83-714

In Stock

[Other Coating Options](#)

-

1

+

C\$91.00

ADD TO CART

Qty 1-10

C\$91.00

Qty 11+

C\$80.50

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):

3.00 ±0.015

Effective Focal Length EFL (mm):

4.50 @ 633nm

Numerical Aperture NA:

0.30

Substrate: D-ZK3
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 633
Coating: BBAR (600-1050nm)
Coating Specification: R _{abs} <1.0% @ 600 - 1050nm
Surface Quality: 60-40
Clear Aperture CA (mm): 2.70
Edge Thickness ET (mm): 1.33
Center Thickness CT (mm): 1.78 ±0.05
f/#: 1.67
Bevel: Protective bevel as needed
Lightpath Lens Code: 354996
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Working Distance (mm): 3.500
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant