

LightPath 355397 | 7.2mm Dia., 0.30 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-121** ☐ In Stock

[Other Coating Options](#)

1

C\$91.00

ADD TO CART

Qty 1-10
C\$91.00
Qty 11+
C\$80.50
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
7.20 ±0.020

Effective Focal Length EFL (mm):
11.00 @670nm

Numerical Aperture NA:
0.3

Substrate: D-ZLaF52LA
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 670
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality: 60-40
Clear Aperture CA (mm): 6.68
Edge Thickness ET (mm): 1.28
Center Thickness CT (mm): 1.95 ±0.05
f/#: 1.67
Bevel: Protective bevel as needed
Compatible Window: Thickness: 0.28 (t) (mm) Material: BK7
Distance from Window to Lens (D) (mm): 9.346
Lightpath Lens Code: 355397
Operating Temperature (°C): ≤200
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Typical Applications: Collimate or Focus Laser Light
Working Distance (mm): 10
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant