

0.40 NA, 6.25mm FL, HOYA Molded Glass Aspheric Lens

See More by [Hoya](#)



HOYA Molded Glass Aspheric Lenses

Stock **#13-586** ☐ In Stock

-

1

+

C\$133.00

ADD TO CART

Qty 1-10

C\$133.00

Qty 11+

C\$105.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
6.38 +0.00/-0.02

Effective Focal Length EFL (mm):
6.25 @ 780nm

Numerical Aperture NA:
0.40

Substrate: M-LaF81
Aspheric Design Wavelength (nm): 780
Coating: BBAR (680-880nm)
Coating Specification: Ravg <1% @ 680 - 880nm (typical)
Center Thickness CT (mm): 2.50
f#: 0.98
Bevel: Protective bevel as needed
Type: Aspheric Lens
Wavelength Range (nm): 680 - 880
Working Distance (mm): 4.57
Conjugate Distance: 0
Transmitted Wavefront, RMS @ 632.8nm: 0.04λ
Model Number: AH11_Z

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View