

0.420 - 1.08 μ m, 300mW, Silicon Power Detector



Photodetector with Attenuator

Stock **#89-309** **1 In Stock**

1 **C\$1,820⁰⁰**

ADD TO CART

Volume Pricing

Qty 1-4	C\$1,820.00 each
Qty 5+	C\$1,638.00 each
Need More?	Request Quote

Product Downloads

General

OD 1.0 Attenuator

Filters Included :

Premier ([#89-306](#))
Deluxe ([#89-305](#))
USB ([#89-307](#))

Compatible Meters:

Physical & Mechanical Properties

38.1 Dia. x27.4 T

Dimensions (mm):

130	Weight (g):
0.13	Weight (kg):
10	Active Area (mm):
Optical Properties	
420 - 1080	Wavelength Range (nm):
0.420 - 1.08	Wavelength Range (µm):
Sensor	
Silicon	Type of Sensor:
Electrical	
300	Maximum Incident Beam Power (mW):
0.3	Maximum Incident Beam Power (W):
100	Maximum Incident Power Density (W/cm²):
0.1	Maximum Incident Power Density (kW/cm²):
10 pW	Noise Level:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:

Product Details

- Photodetectors, Thermopiles, and Pyroelectric Detectors
- Various Sizes Across Wide Range of Sensitivities
- Compatible with [Edmund Optics Laser Power and Energy Meters](#)
- [Wireless Power and Energy Detectors](#) Also Available

Edmund Optics® Power and Energy Detectors provide fast response times and accurate measurements for beam analysis. Versatile pyroelectric energy detectors with broadband coatings are optimized for low to high power densities. Photodetectors, thermopile detectors and volume absorbers can be used with a variety of laser powers ranging from the nanowatts to multi-kilowatts.

Edmund Optics® Power and Energy Detectors feature high-performance pyroelectric infrared sensors and other detector technologies designed for accurate laser power and energy measurements across UV, visible, and IR spectra. These detectors are ideal for applications requiring precise monitoring of continuous-wave (CW), pulsed, or modulated laser output. These energy and power detectors have fast response times, are plug-and-play ready, and provide reliable readings across different wavelength bands and power ranges.

This detector family includes three core sensor types—**silicon**, **thermopile**, and **pyroelectric**—each optimized for specific measurement needs. **Silicon detectors** offer high sensitivity and fast response for low-power, visible to NIR CW lasers. **Thermopile detectors** provide a broadband, flat spectral response ideal for measuring average power from CW and high-power lasers, including in the mid-IR range. **Pyroelectric detectors** are designed for pulsed laser measurements, detecting rapid thermal changes for accurate energy readings. Choosing the right detector depends on your laser source and measurement goals, and Edmund Optics provides technical guidance and support to help you make the best selection.