

LightPath 354125 | 11mm Dia., 0.50 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#33-426** ☐ **In Stock**

[Other Coating Options](#)

-

1

+

C\$197.40

ADD TO CART

Qty 1-10
C\$197.40
Qty 11+
C\$174.30
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
11.00 ±0.015

Effective Focal Length EFL (mm):
10.00 @ 633nm

Numerical Aperture NA:
0.5

Substrate:  D-ZK3
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 633
Coating: BBAR (600-1050nm)
Coating Specification: R _{abs} <1.0% @ 600 - 1050nm
Surface Quality: 60-40
Clear Aperture CA (mm): 10
Edge Thickness ET (mm): 1.092
Center Thickness CT (mm): 3.64 ±0.40
f/#: 1.00
Bevel: Protective bevel as needed
Compatible Window: Thickness: 0.25 (t) (mm) Material: B-K7
Lightpath Lens Code: 354125
Operating Temperature (°C): ≤200
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Typical Applications: Collimate or Focus Laser Light
Working Distance (mm): 7.8
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant