

0.50 NA, 4.2mm FL, HOYA Molded Glass Aspheric Lens

See More by [Hoya](#)



HOYA Molded Glass Aspheric Lenses

Stock **#13-587** ☐ In Stock

-

1

+

C\$140.00

ADD TO CART

Qty 1-10

C\$140.00

Qty 11+

C\$110.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
6.38 +0.00/-0.02

Effective Focal Length EFL (mm):
4.20 @ 780nm

Numerical Aperture NA:
0.50

Substrate: M-LaF81
Aspheric Design Wavelength (nm): 780
Coating: BBAR (680-880nm)
Coating Specification: Ravg <1% @ 680 - 880nm (typical)
Center Thickness CT (mm): 2.56
f/#: 0.66
Bevel: Protective bevel as needed
Type: Aspheric Lens
Wavelength Range (nm): 680 - 880
Working Distance (mm): 2.00
Conjugate Distance: 0
Transmitted Wavefront, RMS @ 632.8nm: 0.04λ
Model Number: AH4_Z

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View