

[See all 4 Products in Family](#)

0.50 NA Patchcord 400 Micron Fiber w/ SMA Connector



Stock **#28-741** [CONTACT US](#)

-

1

+

C\$421^{.40}

ADD TO CART

Volume Pricing	
Qty 1+	C\$421.40 each
Need More?	Request Quote

Product Downloads

General

Type:

Patchcord

Physical & Mechanical Properties

Minimum Bend Radius (mm):

43 (Short Term)
86 (Long Term)

Length (m):

1.5

Optical Properties

0.50	Numerical Aperture NA:
VIS-NIR	Wavelength:
300 - 1200	Wavelength Range (nm):
Hardware & Interface Connectivity	
SMA905	Connector:
Environmental & Durability Factors	
-40 to +85	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

Product Details

- 420 - 900nm Illumination with Converted LED
- Up to 20mW Output Power from a 1mm Multimode Fiber
- Light Coupling with 50µm – 1mm Core Diameter Multimode Fibers
- Ideal for Spectroscopy Applications

The Fiber Coupled Broadband LED Light Source utilizes a VIS/NIR phosphor converter to convert the output of a 450nm LED chip into a broad 420 – 900nm spectrum. This light source provides highly efficient coupling with SMA connected multimode fibers with diameters of 50µm to 1mm and a numerical aperture (NA) up to 0.50, and features an output up to 20mW with a 1mm, 0.5 NA fiber. Featuring a built-in microprocessor, this light source can also be operated as a free-running stroboscope with an adjustable duty cycle and frequency up to 1kHz. The Fiber Coupled Broadband LED Light Source is a powerful alternative to halogen light sources and is ideal for VIS/NIR spectroscopy applications such as protein characterization, oxygen monitoring in marine ecosystems, and respiratory gas analysis. This light source can be controlled manually with the multifunctional rotating knob, directly via programming through a serial RS232 interface or with the provided user-friendly software interface.