See all 77 Products in Family

LightPath 355230 | 6.33mm Dia., 0.55 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by Lightpath®

Precision Molded Aspheric Lenses

Stock **#87-153** **20+ In Stock**

Other Coating Options

- 1 + **C$119**.00

ADD TO CART

Volume Pricing	
Qty 1-10	**C$119.00** each
Qty 11-49	**C$107.10** each
Need More?	Request Quote

Product Downloads

General

Compatible Window:

Thickness: 0.25 (t) (mm)
Material: BK7

Lightpath Lens Code:

355230

Type:

Aspheric Lens

Typical Applications:
Collimate or Focus Laser Light

Physical & Mechanical Properties

Diameter (mm):
6.33 ±0.020

Clear Aperture CA (mm):
5.07

Edge Thickness ET (mm):
1.67

Center Thickness CT (mm):
2.71 ±0.05

Bevel:
Protective as needed

Distance from Window to Lens (D) (mm):
2.049

Optical Properties

Effective Focal Length EFL (mm):
4.51 @ 780nm

Numerical Aperture NA:
0.55

Substrate:
D-ZLaF52LA

Focal Length Tolerance (%):
±1

Aspheric Design Wavelength (nm):
780

Coating:
BBAR (350-700nm)

Coating Specification:
R_{avg} ≤0.5% @ 350 - 700nm

Surface Quality:
40-20

f/#:
0.91

Wavelength Range (nm):
350 - 700

Working Distance (mm):
3.08

Conjugate Distance:
Infinite

Transmitted Wavefront Error (λ, RMS):
< 0.09

Environmental & Durability Factors

Operating Temperature (°C):
≤200

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 247:
Compliant

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information


WD
CT
D
CA
OD
ET
t