

LightPath 354105 | 7.2mm Dia., 0.56 NA, BBAR (1050-1600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-147** ☐ In Stock

[Other Coating Options](#)

-

1

+

C\$126.00

ADD TO CART

Qty 1-10

C\$126.00

Qty 11+

C\$110.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
7.20 ±0.020

Effective Focal Length EFL (mm):
5.50 @ 633nm

Numerical Aperture NA:
0.56

Substrate: D-ZK3
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 633
Coating: BBAR (1050-1600nm)
Coating Specification: R _{abs} <1.0% @ 1050 - 1600nm
Surface Quality: 40-20
Clear Aperture CA (mm): 6
Edge Thickness ET (mm): 1.29
Center Thickness CT (mm): 2.94 ±0.03
f/#: 0.89
Bevel: Protective bevel as needed
Compatible Window: Thickness: 0.25 (t) (mm) Material: BK7
Distance from Window to Lens (D) (mm): 3.091
Lightpath Lens Code: 354105
Operating Temperature (°C): ≤200
Type: Aspheric Lens
Wavelength Range (nm): 1050 - 1600
Typical Applications: Collimate or Focus Laser Light
Working Distance (mm): 3.7
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant