

0.6 OD, 25mm Dia., Precision Anti-Reflection (AR) Coated Absorptive ND Filter



Precision Absorptive Neutral Density (ND) Filters

Stock **#16-057** ☐ In Stock

-

1

+

C\$140.00

ADD TO CART

Qty 1-10
C\$140.00
Qty 11+
C\$126.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.00

Optical Density OD (Average):
0.6 ±10% @ 550nm

Glass/Filter Number:
[SCHOTT NG5](#)

Substrate: ☐

ND Filter Glass
Coating: BBAR (450-700nm)
Index of Refraction n_d: 1.50
Surface Quality: 80-50
Transformation Temperature (°C): 474
Thickness (mm): 2.54 (nominal)
Transmission (%): 25.12
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Clear Aperture (%): 90
Transmitted Wavefront, P-V: $\lambda/4$
Parallelism (arcsec): <30
Coating Specification: $R_{avg} \leq 1.0\%$ @ 450 - 700nm @ 0°

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant