


0.6" x 0.6", 0.2" FL, Aspheric Fresnel Lens



0.6" x 0.6", 0.2" FL, Aspheric Fresnel Lens, #43-021

Stock **#43-021** ☐ In Stock

1

C\$46.90

ADD TO CART

Qty 1-10

C\$46.90

Qty 11+

C\$40.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Effective Focal Length EFL (mm):

5.08

Substrate: ☐

Acrylic

Coating:

Uncoated

Type:

Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.06
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 0.6 x 0.6
Dimensions (mm): 15.24 x 15.24
Effective Diameter (inches): Consists of three 0.2" fresnel patterns
Effective Focal Length EFL (inches): 0.20
Groove Density (grooves/inch): 400
Index of Refraction n_d: 1.49
Operating Temperature (°C): 80 (Maximum)
Thickness Tolerance (%): ±40
Transmission (%): 85 (Typical)
Typical Applications: Designed with infinite conjugate on flat side

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View