

[All Products](#) / [Lab and Production](#) / [Optical Adhesives](#) / [Norland Optical Adhesives](#)

[See all 48 Products in Family](#)

Norland Optical Adhesive NOA 68TH, 1 oz. Application Bottle

See More by [Norland](#)



Norland Optical Adhesive NOA68TH, 1 oz. Application Bottle, #14-791

Stock **#14-791** ☐ In Stock

-

1

+

C\$121.80

ADD TO CART

Qty 1-4
C\$121.80
Qty 5+
C\$116.20
Volume Pricing
Request Quote

Get Product Downloads

Size (oz): 1
Glass Bonding: Excellent
Metal Bonding: Good

Plastic Bonding: Excellent/Good
Viscosity (cps): 20,000 - 25,000
Durability: Flexible
Index of Refraction n_d: 1.54 @ 589nm
Norland Number: 68TH
Shelf Life: 4 months
Type: Bottle
Typical Applications: Screen printable, high viscosity optical adhesive that can be UV cured and/or heat cured.
Note: Heat curing (-H suffix) adhesives are oxygen inhibited. If used on the surface of a substrate, the adhesive will need to be cured under an inert atmosphere (like nitrogen) to fully cure.
Absorption Range (nm): 350 - 380
Bonding Type: Plastic to Plastic/Glass
Energy for Full Cure (J/cm²): 4.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant