

10 x 10mm, 300µm Pitch, 10.1° Divergence, Cyl. Microlens Array



Stock **#86-841** ☐ In Stock

-

1

+

C\$987.00

ADD TO CART

Qty 1-10
C\$987.00
Qty 11+
C\$868.00
Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
0.80

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Coating:
Uncoated

Type:
Lens Array

Wavelength Range (nm): 200 - 2200
Dimensional Tolerance (mm): ±0.05
Dimensions (mm): 10.0 x 10.0
Divergence Angle (°): ±10.1
Pitch (µm): 300.00
Pitch Tolerance (µm): ±0.25
Radius R (mm): 0.380
Thickness (mm): 1.20
Thickness Tolerance (mm): ±0.05

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View