

12 x 12mm, 500µm Pitch, 2.3° Divergence, Cyl. Microlens Array



Stock **#23-871** ☐ In Stock

-

1

+

C\$749.00

ADD TO CART

Qty 1-10
C\$749.00
Qty 11+
C\$674.80
Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
12.20 @ 1064nm

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Coating:
Uncoated

Type:
Lens Array (One Sided)

Wavelength Range (nm): 200 - 2200
Dimensional Tolerance (mm): ±0.1
Dimensions (mm): 12.0 x 12.0
Divergence Angle (°): 2.3 (Full Width)
Pitch (µm): 500
Radius R (mm): 5.500
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View