

TECHSPEC®

10 x 15mm, 0.50 Numerical Aperture, Uncoated, Truncated Precision Aspheric Lens



Stock **#17-307** ☐ In Stock

-

1

+

C\$364.00

ADD TO CART

Qty 1-5
C\$364.00
Qty 6+
C\$291.20
Volume Pricing
Request Quote

Get Product Downloads



Dimensions (mm):
10.00 x 15.00

Effective Focal Length EFL (mm):
15.00 @ 587.6nm

Numerical Aperture NA:
0.50

Back Focal Length BFL (mm): 10.22
Substrate: N-SF6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 8.00 x 13.00
Edge Thickness ET (mm): 6.21
Center Thickness CT (mm): 8.62 ±0.10
f#: 1.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 390 - 2500
Conjugate Distance: Infinite
Power (diopters): 66.67

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View