


10 x 10mm Aperture, Quartz Lyot Depolarizer



Stock **#65-893** **2 In Stock**

1 C\$1,022.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$1,022.00 each
Qty 6+	C\$826.00 each
Need More?	Request Quote

Product Downloads

General

Depolarizer **Type:**

Physical & Mechanical Properties

10.0 x 10.0 **Clear Aperture CA (mm):**

6.00 **Length (mm):**

±0.2 **Dimensional Tolerance (mm):**

Crystalline **Construction:**

<20 **Parallelism (arcsec):**

Optical Properties

Crystal Quartz **Substrate:** □

20-10 **Surface Quality:**

200 - 2300 **Wavelength Range (nm):**

λ/10 **Surface Flatness (P-V):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Lyot Depolarizers are not suitable for monochromatic light.
- Turn Polarized Light into Non-Polarized (Unpolarized) Light
 - Designed for Polychromatic Light
 - UV to IR Wavelength Range

Consisting of two quartz waveplates bonded together, Lyot Depolarizers are passive optical components that transform polarized or partially polarized light into non-polarized (unpolarized) light. The thickness ratio of the two waveplates is 2:1. They are positioned such that their optical axes are oriented 45° apart, creating various degrees of elliptically and linearly polarized light, and eliminating the polarization of the input beam.

Note: Lyot Depolarizers are not suitable for monochromatic light.

Lyot Depolarizers are designed for polychromatic light from 200 - 2300nm. Each Lyot Depolarizer features a minimum wavelength bandwidth of 50nm, which represents approximately 85% depolarization. A bandwidth of greater than 100nm is required for complete depolarization.

Technical Information

