

TECHSPEC[®]

10 x 15mm, 0.66 Numerical Aperture, Uncoated, Truncated Precision Aspheric Lens



Stock #17-309 10 In Stock

-

1

+

C\$436⁻⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$436.80 each
Qty 6-25	C\$350.00 each
Qty 26-49	C\$329.00 each
Need More?	Request Quote

Product Downloads

General	
Aspheric Lens	Type:
Physical & Mechanical Properties	
10.00 x 15.00	Dimensions (mm):
<1	Centering (arcmin):

8.00 x 13.00	Clear Aperture CA (mm):
6.67	Edge Thickness ET (mm):
10.02 ±0.10	Center Thickness CT (mm):
Protective as needed	Bevel:

Plano	Shape of Back Surface:
-------	------------------------

Optical Properties

11.25 @ 587.6nm	Effective Focal Length EFL (mm):
0.66	Numerical Aperture NA:

5.71	Back Focal Length BFL (mm):
N-SF6	Substrate:

0.4λ	Asphere Figure Error, RMS @ 632.8nm:
Uncoated	Coating:

40-20	Surface Quality:
0.75	f/#:

390 - 2500	Wavelength Range (nm):
Infinite	Conjugate Distance:

88.89	Power (diopters):
-------	-------------------

Regulatory Compliance


View	Certificate of Conformance:
------	-----------------------------


Product Details

- Rectangular and Square Aspheres in 5 x5mm to 12.5 x25mm sizes
- Precision Grade Aspheric Figure Error
- Ideal for Integration into Space Sensitive Laser Systems

TECHSPEC® Truncated Precision Aspheric Lenses are truncated versions of our [TECHSPEC Precision Aspheric Lenses](#). These aspheric lenses are CNC polished to achieve a 0.4λ (Waves) RMS aspheric figure error and then cut to square or rectangular sizes. The precision aspheric figure error of these lenses makes them advantageous for demanding imaging or laser systems requiring spherical aberration correction. TECHSPEC Truncated Precision Aspheric Lenses with their space saving form factors are ideal for integration into medical devices, life science instrumentation, and industrial laser systems. Please contact us if your application requires a [TECHSPEC Aspheric Lens](#) truncated to meet specific size requirements.

Technical Information





Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).