

100 x 100mm, 1.1mm Thick, Uncoated, SCHOTT Xensation® Chemically Strengthened Window

See More by [SCHOTT Optical Components](#)



Stock **#17-263** [CONTACT US](#)

- 1 +

C\$56.00

ADD TO CART

Qty 1-5
C\$56.00
Qty 6+
C\$44.80
Volume Pricing
Request Quote

Get Product Downloads

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm):
90 x 90

Dimensions (mm): 100.00 x 100.00
Thickness (mm): 1.10 Nominal
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 8.8 (+20 to +300°C)
Density (g/cm³): 2.48
Edges: Fine Ground
Index of Refraction n_d: 1.51
Knoop Hardness (kg/mm²): 639
Poisson's Ratio: 0.215
Substrate: SCHOTT Xensation®
Surface Quality: 80-50
Transformation Temperature (°C): 615
Type: Protective Window
Wavelength Range (nm): 380 - 840
Young's Modulus (GPa): 74
Length (mm): 100.00
Width (mm): 100.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant