

[See all 9 Products in Family](#)

# 100 x 150mm, White, EuroBrite™ Spot Light

See More by [Advanced Illumination](#)



White AI EuroBrite Spot Light

Stock **#33-453** **2 In Stock**

⊖ 1 ⊕ C\$875<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	C\$875.00 each
Need More?	<a href="#">Request Quote</a>

**Note:** This item requires accessories for use | [Learn More](#)

## Product Downloads

### General

50,000 **Operating Lifetime (hours):**

SL-S100150M-WHI **Model Number:**

LED Illuminator **Type of Illumination:**

**Note:**  
See Technical Information Tab for Typical Intensity

Advanced Illumination	<b>Manufacturer:</b>
Spot Light	<b>Geometry:</b>
Strobed or Constant	<b>Illumination Mode:</b>

## Physical & Mechanical Properties

150 x 139 x 30	<b>Dimensions (mm):</b>
253.00	<b>Weight (g):</b>
100 x 150	<b>Active Area (mm):</b>

## Optical Properties

White	<b>Color:</b>
-------	---------------

## Electrical

0.42 - 0.49A	<b>Maximum Input Current:</b>
10% @ 0.7V, 100% @ 10V	<b>Analog Intensity Control:</b>
10µm	<b>Trigger-to-Pulse Latency:</b>

## Hardware & Interface Connectivity

Flying Leads	<b>Connector:</b>
24V nominal (min. 22 / max. 28)	<b>Input Voltage (V):</b>

Power Supply Required and Sold Separately. USA: <a href="#">#66-855</a> Europe: <a href="#">#66-855</a> Japan: <a href="#">#89-513</a> Korea: <a href="#">#33-773</a> China: <a href="#">#66-855</a>	<b>Power Supply:</b>
---	----------------------

## Environmental & Durability Factors

0 - 60	<b>Operating Temperature (°C):</b>
IP67	<b>Environmental Rating:</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Contains SVHC(s)</a>	<b>Reach 233:</b>

## Product Details

- Daisy Chain up to Four 100 x 150mm Units
- Requires No Heat Sink
- Available in White, Red, and Blue

Advanced Illumination EuroBrite™ Spot Light illuminators feature on-board smart drivers functional during strobe and continuous operation modes making them ideal for the most demanding performance constraints. Adaptive OverDrive™ allows for power optimization while in strobing mode, and Adaptive Thermal Feedback™ gives operational current control to the user, preventing overheating and eliminating the need for a heat sink. These Advanced Illumination EuroBrite™ Spot Light illuminators feature a ruggedized, sealed enclosure, and are available in white, red, or blue versions. The ability to operate four 100 x 150mm units connected to one another, and an analog dimming control operable in both strobe and continuous modes add to illuminator's customizability.

**Note:** A 24V power supply is required.

## Technical Information

Typical Intensity				
Size	50 x 75mm	50 x 75mm	50 x 75mm	100 x 150mm
Working Distance	100mm	300mm	600mm	600mm
Area	79 x 56mm	117 x 99mm	ø198mm	325 x 198mm
Typical Irradiance (W/M <sup>2</sup> )	100.0	74	28	147

Typical Illuminance (kLux)	34.0	25	10	49
----------------------------	------	----	----	----

---

;