

TECHSPEC® 100mm Dia., 0.50 Numerical Aperture VIS Coated, Aspheric Lens



Stock **#22-708** ☐ In Stock

[Other Coating Options](#)

1

C\$1,470.00

ADD TO CART

Qty 1-5
C\$1,470.00
Qty 6+
C\$1,176.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
100.00 +0.0/-0.1

Effective Focal Length EFL (mm):
100.00 @587.6nm

Numerical Aperture NA:
0.50

Back Focal Length BFL (mm): 78.18
Substrate: N-BK7
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: BBAR (425-675nm)
Coating Specification: R _{avg} ≤1.5% @ 425 - 675nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 90
Edge Thickness ET (mm): 5.90
Center Thickness CT (mm): 33.10 ±0.1
f#: 1.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 350 - 2200
Conjugate Distance: Infinite
Power (diopters): 10.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant