


1000μm with 1 Fiber, Optical Grade Plastic Light Guide



Stock **#02-536** ☐ In Stock

- 1 +

C\$5.46

ADD TO CART

Qty 1+

C\$5.46

Volume Pricing

[Request Quote](#)

Get Product Downloads

Acceptance Angle (°):
61.00

Minimum Bend Radius (mm):
55.00

Substrate: ☐
Acrylic

Attenuation (dB/m):
0.21

Numerical Aperture NA:
0.51

Number of Fibers: 1.00
Operating Temperature (°C): -55 to +70
Outer Diameter (mm): 2.2
Core Diameter (µm): 980.00
Fiber Diameter (µm): 1000.00
Length (ft): Cut to Order, Minimum 10
Construction: Black Polyethylene Jacket
Index of Refraction n_d - Core: 1.492
Index of Refraction n_d - Cladding: 1.402
Attenuation (dB/km): 150 - 300 (@ 650nm)
Numerical Aperture (NA) Tolerance: ±0.03
Diameter Tolerance (%): ±6

Regulatory Compliance

RoHS 2015: Compliant
Reach 197: Compliant
Certificate of Conformance: View