

TECHSPEC® 10.0mm Dia. x 12.5mm FL, VIS-NIR Coated, Plano-Convex Lens



Stock **#38-489** ☐ **In Stock**
[Other Coating Options](#)

1 **C\$58.10**

ADD TO CART

Qty 1-9
C\$58.10
Qty 10+
C\$52.15
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
10.00 +0.0/-0.025

Effective Focal Length EFL (mm):
12.50 @ 587.6nm

Back Focal Length BFL (mm): 10.99
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.70 ±0.05
Edge Thickness ET (mm): 1.33
Radius R₁ (mm): 9.81
Clear Aperture CA (mm): 9
f#: 1.25
Numerical Aperture NA: 0.40
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant