

100mm FL, 1064nm Edmund Optics® F-Theta Lens



Stock **#15-179** ☐ In Stock

-

1

+

C\$1,141.00

ADD TO CART

Qty 1-4
C\$1,141.00
Qty 5+
C\$1,026.20
Volume Pricing
Request Quote

Get Product Downloads

Design Wavelength DWL (nm):
1064

Focal Length FL (mm):
101.60

Maximum Diameter (mm):
87

Scan Angle (°):
±22.68

Scan Field (mm): 56.5 x 56.5
Mounting Threads: M85 x 1.0
Telecentricity (°): Not Specified
Transmission (%): ≥95
Type: F-Theta Lens
Working Distance (mm): 107.9
Wavelength Range (nm): 1064
Range Distance (mm): 126.9
Focus Size Diameter, 1/e² (μm): 17
Input Beam Diameter, 1/e² (mm): 12
Maximum Length (mm): 52.3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View