See all 5 Products in Family

100mm FL, 1064nm Edmund Optics® F-Theta Lens

Stock **#15-179** CLEARANCE CONTACT US

- 1 + **C$889**.00

ADD TO CART

Volume Pricing	
Qty 1+	**C$889.00** each
Need More?	Request Quote

Product Downloads

General

Type:
F-Theta Lens

Physical & Mechanical Properties

Maximum Diameter (mm):
87

Flange Distance (mm):
126.9

Input Beam Diameter, $1/e^2$ (mm):
12

Maximum Length (mm):

52.3

Optical Properties

Focal Length FL (mm):
101.60

Scan Angle (°):
±22.68

Scan Field (mm):
56.5 x 56.5

Telecentricity (°):
Not Specified

Transmission (%):
≥95

Working Distance (mm):
107.9

Design Wavelength DWL (nm):
1064

Wavelength Range (nm):
1064

Focus Size Diameter, $1/e^2$ (µm):
17

Threading & Mounting

Mounting Threads:
M85 x 1.0

Regulatory Compliance

Certificate of Conformance:
View

Product Details

- Ideal for Laser Scanning Applications
- Diffraction Limited Across the Scan Field with Low Wavefront Error
- Long Working Distances and Large Scan Areas
- **Galvanometers**, **Beam Expanders**, and **Laser Sources** Also Available

Edmund Optics® F-Theta Lenses are designed to provide flat fields at the image plane of scanning systems and are used in conjunction with **galvanometers**, **beam expanders**, and **laser sources**. These F-Theta Lenses feature compact form factors, offer a wide range of focal lengths up to 273mm, and large scan fields up to 164mm (X) x 164mm (Y). Optimized for common fiber laser sources and Nd:YAG fundamental or second harmonic, these lenses are available in design wavelengths of 532nm and 1064nm with common mounting threads for easy integration into galvo systems. Edmund Optics® F-Theta Lenses are a cost-effective solution for laser scanning and laser processing applications including laser marking, engraving, cutting, drilling, and 3D modeling.

;