

101 x 127mm, Extended Hot Mirror



Extended Hot Mirrors

Stock **#47-304** [CONTACT US](#)

-

1

+

C\$414⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-9	C\$414.40 each
Qty 10-25	C\$372.40 each
Qty 26-49	C\$354.20 each
Need More?	Request Quote

Product Downloads

General	
Shortpass Filter	Type:
Physical & Mechanical Properties	
3.30 ±0.2	Thickness (mm):
101.0 x 127.0	Dimensions (mm):

≥85	Clear Aperture (%):
±0.5	Dimensional Tolerance (mm):
Seamed	Edges:
127.00	Length (mm):

101.00	Width (mm):
--------	-------------

Optical Properties

Dielectric	Coating Type:
Hot Mirror, 0°	Coating:

4 - 6λ	Surface Flatness (P-V):
425 - 1600	Wavelength Range (nm):

	Substrate: ☐
0.00	Angle of Incidence (°):

R _{avg} ≥90% @ 750 - 1150nm R _{avg} ≥80% @ 1200 - 1600nm T _{avg} ≥85% @ 425 - 675nm	Coating Specification:
80-50	Surface Quality:

Regulatory Compliance

	RoHS 2015:
	Certificate of Conformance:

	Reach 247:
---	------------


Product Details

- Improved NIR Reflectance Over Standard Hot Mirrors
- Operating Temperatures up to 230°C
- Neutral Color for 5500K or 3200K Sources to ±250K

Extended Hot Mirrors are designed to reduce the heat in an optical system without sacrificing the system's visible output. While typical hot mirrors reflect from 750nm to approximately 1250nm, Extended Hot Mirrors further reduce heat by extending the reflection range to approximately 1750nm.

Hot mirrors are crucial in many projection and illumination systems where high levels of heat can quickly damage sensitive components. Hot mirrors are specially coated to transmit visible light while reflecting the NIR, a major attributor to heat generation. By using a hot mirror, heat levels are limited with minimum impact on the overall system performance.

Technical Information



Quote Your Size

Compatible Mounts

;