

101.6mm Length, M6 and M6, Steel Post



Stock #72-776 NEW **5 In Stock**

⊖ 1 ⊕ C\$9⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$9.80 each
Need More?	Request Quote

Product Downloads

General

Metric Type:

Physical & Mechanical Properties

101.60 ±0.1 Length (mm):

4 Length (inches):

12.70 -0.02/-0.05 Diameter (mm):

Diameter (inches):

Threading & Mounting

Male Thread:

Thread 1: M6 x 1
Thread 2: M6 x 1

Regulatory Compliance

RoHS 2015:[Compliant](#)**Certificate of Conformance:**[View](#)**Reach 247:**[Compliant](#)

Product Details

- English or Metric Versions Options Available
- Wide Variety of Lengths Available from 25.4 to 304.8mm (1" to 12").
- Removable Top and Bottom Set Screws Available

Stainless Steel Optical Mounting Posts are a practical and straightforward way to integrate optical assemblies and photonic equipment onto an [optical lab table](#) or [breadboard](#). All mounting posts are 12.7 mm (0.5") in diameter and are offered in various lengths from 25.4 to 304.8mm (1" to 12"). Each mounting post features a female thread on each end with a set screw preinstalled, making it simple to mount components with counterbore or tapped hole mounting features. Stainless Steel Optical Mounting Posts can be used with [Post Holders](#) to allow for height adjustment of the optical component, and for a secure connection with the optical benchtop. Thread values (M4 x 0.7/M6 x 1.0 for Metric; 8-32/¼-20 for English) are laser-engraved on the ends of each post for quick identification and integration.

Note: All posts have a through-hole that allows an Allen wrench, 5.5mm or 7/32" key size, or other tools to rotate the post easily.