

TECHSPEC® 101.6 x 101.6mm EFL 90° Protected Gold 100Å Off-Axis Parabolic Mirror



Stock **#35-573** ☐ In Stock

[Other Coating Options](#)

1 **C\$1,449.00**

ADD TO CART

Qty 1-5
C\$1,449.00
Qty 6+
C\$1,304.10
Volume Pricing
Request Quote

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
101.60 +0.00/-0.38

Effective Focal Length EFL (mm):
101.60

Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 101.60
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Coating Specification: R _{avg} ≥94% @ 700 - 800nm R _{avg} ≥97% @ 800 - 2,000nm R _{avg} ≥98% @ 2,000 - 12,000nm
Off-Set Angle (°): 90
Parent Focal Length PFL (mm): 50.8
Surface Figure, RMS: 1λ
Surface Roughness (Angstroms): <100 RMS
Wavelength Range (nm): 700 - 10000
Clear Aperture (%): 90
Surface Quality: 80-50
Compatible Mounting Plates: #83-977
Substrate: Aluminum 6061-T6
Y Offset (mm): 101.6
Reflected Wavefront, RMS: 2λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant