

TECHSPEC® 1064nm, 0° 25.4mm Dia. Nd:YAG IBS Low Loss Laser Line Mirror



Stock **#89-452** ☐ In Stock

1 **C\$280.00**

ADD TO CART

Qty 1-5
C\$280.00
Qty 6+
C\$245.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Quality:
20-10

Type:
Laser Mirror

Parallelism (arcmin):
<1

Clear Aperture (%):

>90
Durability: ML-C-675A
Back Surface: Commercial Polish
Reflection at DWL (%): 99.95
Reflectivity (Rs%): >99.95
Reflectivity (Rp%): >99.95
Reflectivity (Rs% Rp%): >99.5
Coating Specification: Rs >99.95% @ 1064nm Rp >99.95% @ 1064nm
Wavelength Range (nm): 1030 - 1064
Surface Flatness (P-V): λ/8
Coating Type: Dielectric
Coating: Laser Mirror (1030-1064nm)
Design Wavelength DWL (nm): 1064
Diameter (mm): 25.40 +0.0/-0.1
Thickness (mm): 5.00 ±0.1
Angle of Incidence (°): 0
Substrate: ☐ Fused Silica (Corning 7980)
Damage Threshold, By Design: ☐ >12 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant