


# 1064nm, 15mm Dia., Round Output, Diffractive Diffuser



HOLO/OR Diffractive Diffusers

Stock #14-682  In Stock

1  **C\$1,820.00**

**ADD TO CART**

Qty 1+  
C\$1,820.00

Volume Pricing  
[Request Quote](#)

Get Product Downloads



**Clear Aperture CA (mm):**  
13.00

**Coating:**  
Laser V-Coat (1064nm)

**Design Wavelength DWL (nm):**  
1064

**Diameter (mm):**  
15.00 +0.05/-0.15

**Substrate:**  
[Fused Silica](#) (Coming 7980)

**Thickness (mm):**  
3.00 ±0.1

**Input Beam Mode:**  
SMor MM

**Minimum Beam Diameter (mm):**  
5

**Output Shape:**  
Round

**Overall Efficiency (%):**  
77

**Full Angle (°):**  
5.27

**Damage Threshold, Reference:**   
[See Link for More Details](#)

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 233:**  
[Compliant](#)

---