

**TECHSPEC® 1064nm 2X – 8X Gemma® Variable Beam Expander**



Stock #15-544 **5 In Stock**

⊖ 1 ⊕ C\$2,653<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	C\$2,653.00 each
Qty 5-24	C\$2,345.00 each
Qty 25-99	C\$2,065.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Beam Expander

Type:

Variable Magnification

Style:

**Physical & Mechanical Properties**

157.50 (without end caps)

Length (mm):

484	<b>Weight (g):</b>
48	<b>Housing Diameter (mm):</b>
<1	<b>Pointing Accuracy (mrad):</b>
<b>Optical Properties</b>	
14.5	<b>Entrance Aperture (mm):</b>
30	<b>Exit Aperture (mm):</b>
2X - 8X	<b>Expansion Power:</b>
<b>Fused Silica</b> (Corning 7980)	<b>Substrate:</b> <input type="checkbox"/>
>97.5 @ DWL	<b>Transmission (%):</b>
Laser V-Coat (1064nm)	<b>Coating:</b>
1064	<b>Design Wavelength DWL (nm):</b>
<b>Transmitted Wavefront, P-V:</b> <N10 for Input Beam 3.5mm (2X-6X) <N10 for Input Beam 2mm (2X-8X)	
1030 - 1100	<b>Wavelength Range (nm):</b>
<b>Coating Specification:</b> R <sub>abs</sub> <0.25% @ 1063 - 1065nm R <sub>avg</sub> <0.5% @ 1030 - 1100nm	
<b>Damage Threshold, By Design:</b> <input type="checkbox"/> 10 J/cm <sup>2</sup> (>3X), 5 J/cm <sup>2</sup> (2-3X) @ 1064nm, 10ns, 20Hz	
Non-Rotating Optics	<b>Divergence Adjustment:</b>
<b>Damage Threshold, Pulsed:</b> 10 J/cm <sup>2</sup> (>3X), 5 J/cm <sup>2</sup> (2-3X) @ 1064nm, 10ns, 20Hz	

<b>Threading &amp; Mounting</b>	
<b>Mounting Threads:</b>	
Input: Male M30 x 1.0 Output: Female M42 x 0.5	

<b>Regulatory Compliance</b>	
<b>Certificate of Conformance:</b>	
<a href="#">View</a>	

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- 2X–8X Continuous Magnification
- Non-Rotating Lenses Minimize Beam Wander
- Compact Galilean Designs with Fixed Housing Length
- **TECHSPEC® Draconis® Broadband Beam Expanders** Also Available

TECHSPEC® Gemma® Variable Beam Expanders are ideal for high power laser applications where magnification changes may be required, such as prototyping or R&D. TECHSPEC Variable Beam Expanders feature M4 transmitted wavefront, Galilean designs, and high laser damage threshold AR coatings to ensure maximum transmittance while minimizing ghost reflections. Additionally, these beam expanders use internal translation and focusing mechanisms to continuously adjust magnification and laser divergence without affecting overall housing length. TECHSPEC® Gemma® Variable Beam Expander allow for continuous magnification change over the full magnification range.

TECHSPEC® Gemma® Variable Beam Expanders can be used to determine a system's required beam magnification in the prototyping phase of development. **TECHSPEC® Draconis® Broadband Beam Expanders** are available for production or OEM implementation. Please contact our Sales Department for custom magnification requirements.