

1064nm, 20mm Dia., 9x9 Spot Matrix, Diffractive Beamsplitter



HOLO/OR Diffractive Beamsplitters

Stock **#14-687** ☐ In Stock

1

C\$1,694.00

ADD TO CART

Qty 1+

C\$1,694.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture CA (mm):
18

Coating:
Laser V-Coat (1064nm)

Design Wavelength DWL (nm):
1064

Diameter (mm):
20.00 +0.05/-0.15

Substrate:
[Fused Silica](#) (Corning 7980)

Thickness (mm): 3.00 ±0.1
Input Beam Mode: SMor MM
Minimum Beam Diameter (mm): 0.37
Overall Efficiency (%): 73
Full Angle (°) : 4.0 x4.0
Output Number of Spots: 9 x9
Separation Angle (°): 0.50 x0.50
Uniformity (%): <13
Zero Order, Relative to the Average (%): 0-100
Damage Threshold, Reference: ☐ See Link for More Details

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant