

TECHSPEC® 1064nm, 45°, 6.35mm Dia., 4mm Thick, Nd:YAG IBS Laser Line Mirror



Stock **#12-525** ☐ In Stock

1

C\$196.00

ADD TO CART

Qty 1-5

C\$196.00

Qty 6+

C\$172.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%):

85
Back Surface: Commercial Polish
Coating Specification: R _{abs} >99.95% @ 1064nm
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror, IBS (1064nm)
Design Wavelength DWL (nm): 1064
Diameter (mm): 6.35 +0.00/-0.10
Thickness (mm): 4.00 ±0.20
Angle of Incidence (°): 45
Substrate: ☐ Fused Silica (Corning 7980)
Damage Threshold, Certified: ☐ 15 J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View