

LightPath 355110 | 1064nm Alignment, 0.40 NA Fiber Collimator w/ FC/PC Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock #64-773 CLEARANCE 20+ In Stock

⊖ 1 ⊕ C\$204⁷⁶

ADD TO CART

Volume Pricing	
Qty 1+	C\$204.76 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

355110

Lightpath Lens Code:

Type:

Lens Included:

#87-127

Physical & Mechanical Properties

Clear Aperture CA (mm):

5.00

Bevel:

Protective as needed

Construction:

304L Stainless Steel Housing

Housing Diameter (mm):

11.00

Housing Length (mm):

13.00

Optical Properties

Effective Focal Length EFL (mm):

6.24 @ 780nm

Numerical Aperture NA:

0.40

Substrate: [D-ZLaF52LA](#)

Coating:

BBAR (1050-1600nm)

Coating Specification:

 $R_{\text{abs}} < 1.0\%$ @ 1050 - 1600nm

Surface Quality:

40-20

f#:

1.25

Wavelength Range (nm):

1050 - 1600

Conjugate Distance:

Infinite

Alignment Wavelength (nm):

1064

Transmitted Wavefront Error (λ , RMS):

< 0.070

Hardware & Interface Connectivity

Connector:

FC/PC

Threading & Mounting

Mount:

M11 x 0.5

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 233:

[Compliant](#)**PRODUCT DETAILS**

- Easy to Integrate
- Models for FC/PC, FC/APC, and SMA Connections Available
- Four Wavelength Ranges Covering 350-1600nm

LightPath® Fiber Optic Collimators are designed to collimate light exiting a fiber to a desired beam diameter or spot size or to focus light into a fiber when used in reverse. The lenses are diffraction limited, so they can achieve spot sizes down to a few microns. Lenses also feature an antireflection coating for low back reflection. LightPath® Fiber Optic Collimators are designed so that they can be used in pairs to couple the input and output light of optical devices. Optimum performance for long-term use is ensured by the factory set and tested lens alignment. Typical applications can include use with fiber coupled lasers and pigtailed receptacles, as well as communications and data transfer.

TECHNICAL INFORMATION

