

[See all 10 Products in Family](#)

# 108mm, 515-540nm JENar™ F-Theta Scanning Lens

See More by [Jenoptik](#)



Stock **#17-023** **8 In Stock**

⊖ 1 ⊕ **CS\$4,277<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	<b>CS\$4,277.00</b> each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

017700-203-26 **Model Number:**

JENar F-Theta **Type:**

**Note:**  
Damage Warning: Not recommended for picosecond and femtosecond laser pulses.

**Protective Window:**  
[#17-699](#): One Included

**Manufacturer:**

## Physical & Mechanical Properties

104.8 +0/-0.1 **Maximum Diameter (mm):**

900 **Weight (g):**

170.9 **Flange Distance (mm):**

15 **Input Beam Diameter, 1/e<sup>2</sup> (mm):**

55.2 **Maximum Length (mm):**

## Optical Properties

108.00 **Focal Length FL (mm):**

40 **Scan Angle (°):**

53 x 53 **Scan Field (mm):**

F-Theta Only: 4.8  
With Scanner: 5.6 **Telecentricity (°):**

130.2 **Working Distance (mm):**

515 - 540 **Wavelength Range (nm):**

**Damage Threshold, By Design:**   
2.5 J/cm<sup>2</sup> \* (τ/[ns])<sup>0.35</sup>  
2.5 MW/cm<sup>2</sup>

75 **Scan Field Diameter (mm):**

7 **Focus Size Diameter, 1/e<sup>2</sup> (μm):**

14700 **GDD Specification (fs<sup>2</sup>):**

2.5 J/cm<sup>2</sup> \* (τ/[ns])<sup>0.35</sup> **Damage Threshold, Pulsed:**

2.5 MW/cm<sup>2</sup> **Damage Threshold, CW:**

## Threading & Mounting

M85 x 1 **Mounting Threads:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Ideal for High-Precision Material Processing and Laser Scanning Applications
- Large Scan Fields Up to 320mm x 320mm
- Wide Range of Focal Lengths from 108mm - 330mm
- [Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses](#) Also Available

Jenoptik JENar™ F-Theta Scanning Lenses are designed to provide flat field at the image plane of scanning systems and are used in conjunction with [galvanometers](#), [beam expanders](#), and [laser sources](#). These F-Theta lenses feature a wide range of focal lengths and large scan fields. Optimized for common Nd:YAG, Yb:doped, and fiber laser sources, these lenses are available in wavelength ranges of 355nm, 515-540nm, and 1030-1080nm. With their patented stackable mounting technology, these lenses compensate for thermal stresses and improve the stability of the optical components, ensuring high-precision adjustment and position control in OEM systems. Jenoptik JENar™ F-Theta Scanning Lenses are ideal for high-precision laser material processing and laser scanning applications.

[Contact us](#) if your application requires Jenoptik JENar™ F-Theta Scanning Lenses or [Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses](#) not shown on our website.