

TECHSPEC®

10mm Dia. 1030nm 45°, Yb:YAG Laser Line Mirror



Yb:YAG ZERODUR Laser Line Mirrors

Stock **#26-894** **9 In Stock**

-

1

+

C\$264⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$264.60 each
Qty 6-25	C\$231.00 each
Need More?	Request Quote

Product Downloads

General

Laser Mirror

Type:

Physical & Mechanical Properties

2.00 +/-0.2

Thickness (mm):

10.00 +0.00/-0.20

Diameter (mm):

Clear Aperture (%):

90	
	Parallelism (arcsec):
30	
Optical Properties	
ZERODUR®	Substrate: ☐
	Surface Quality:
20-10	
	Angle of Incidence (°):
45	
	Coating:
Laser Mirror (1030nm)	
	Design Wavelength DWL (nm):
1030	
	Reflection at DWL (%):
99.8	
	Wavelength Range (nm):
1020 - 1040	
	Surface Flatness (P-V):
λ/10	
	Coating Specification:
R _{abs} > 99.80% @ 1030nm @ 45° AOI R _{avg} > 99.5% @ 1020 - 1040nm @ 45° AOI	
	Coating Type:
Dielectric	
	Damage Threshold, By Design: ☐
20 J/cm ² @ 1030nm, 20ns, 20Hz	
Regulatory Compliance	
	Certificate of Conformance:
View	

Product Details

- ZERODUR® Substrates Provide Near Zero Thermal Expansion
 - >99.8% Reflectivity at Yb:YAG Harmonic Frequencies
 - High Laser Damage Threshold Specifications
- Yb:YAG ZERODUR Laser Line Mirrors combine the extremely low coefficient of thermal expansion of ZERODUR® substrates with the highly reflective TECHSPEC® Yb:YAG mirror coating. Featuring a coefficient of thermal expansion (CTE) of ±0.10 x 10-6/°C these mirrors are great for applications where the optics will be exposed to fluctuating temperatures. The Yb:YAG coating offers a high laser damage threshold compatible with both pulsed and continuous wave lasers. Yb:YAG ZERODUR Laser Line Mirrors are designed with precision polished substrates with λ/10 flatness and 20-10 surface quality. These mirrors are ideal for laser applications that include laser ablation, welding, drilling, cutting, and sintering.