


**TECHSPEC®**

# 10mm Dia., 1.25mm Thick, VIS-EXT Coated, λ/10 Fused Silica Window


 Stock #13-331 **7 In Stock**

- 1 +

 C\$236<sup>.60</sup>
[ADD TO CART](#)

Volume Pricing	
Qty 1-5	C\$236.60 each
Qty 6-25	C\$189.00 each
Qty 26-49	C\$176.40 each
Need More?	<a href="#">Request Quote</a>

Product Downloads	
STEP:step	Curve:pdf
PDF Drawing:pdf	IGES:igs
Curve (xlsx):xlsx	
eDrawing:eprt	
EO Spec Sheet	<a href="#">Download All</a>

## General

<b>Type:</b> Protective Window	<b>Type of Window:</b> Glass
--------------------------------	------------------------------

## Physical & Mechanical Properties

<b>Clear Aperture CA (mm):</b> 8.00	<b>Diameter (mm):</b> 10.00 +0.00/-0.20
<b>Thickness (mm):</b> 1.25 ±0.10	<b>Dimensional Tolerance (mm):</b> +0.00/-0.20
<b>Bevel:</b> Protective as needed	<b>Clear Aperture (%):</b> 80
<b>Edges:</b> Fine Ground	<b>Parallelism (arcsec):</b> <5
<b>Poisson's Ratio:</b> 0.16	<b>Young's Modulus (GPa):</b> 73
<b>Knoop Hardness (kg/mm<sup>2</sup>):</b> 522.00	

## Optical Properties

<b>Coating:</b> VIS-EXT (350-700nm)	<b>Substrate:</b> <a href="#">Fused Silica (Corning 7980)</a>
<b>Index of Refraction (n<sub>d</sub>):</b> 1.458	<b>Surface Quality:</b> 20-10
<b>Transmitted Wavefront, P-V:</b> λ/10	<b>Abbe Number (v<sub>d</sub>):</b> 67.8
<b>Coating Specification:</b> R <sub>avg</sub> <0.5% @ 350 - 700nm	<b>Wavelength Range (nm):</b> 350 - 700

**Damage Threshold, By Design:** 5 J/cm<sup>2</sup> @ 532nm, 10ns ⓘ

## Material Properties

**Density (g/cm<sup>3</sup>):** 2.20

**Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):** 0.52 (+5 to +35°C)  
0.57 (0 to +200°C)  
0.48 (-100 to +200°C)

**Fused Silica Grade:** 7980 0G

## Regulatory Compliance

RoHS 2015: **Compliant**

Certificate of Conformance: **View**

Reach 235: **Compliant**

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


## Product Details

- UV, Visible, and NIR Anti-Reflection Coated Versions Available
- $\lambda/10$  Transmitted Wavefront Distortion
- Circular and Square Sizes from 2mm to 150mm
- **1 $\lambda$**  or  **$\lambda/4$**  UV Fused Silica Windows Also Available

TECHSPEC®  $\lambda/10$  UV Fused Silica Windows feature laser-grade surface quality and parallelism. In addition, these windows will limit the transmitted wavefront distortion to  $\lambda/10$ . The superior transmission characteristics, excellent thermal properties, and high tolerance manufacturing specifications make these windows an excellent choice for more demanding applications. TECHSPEC  $\lambda/10$  UV Fused Silica Windows are available for purchase in circular and square sizes ranging from 2mm to 150mm.. These windows are offered uncoated or with anti-reflection coatings optimized for the UV or visible spectrum.

## Technical Information


### Uncoated Fused Silica Typical Transmission



Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra.

[Click Here to Download Data](#)

### Fused Silica with MgF<sub>2</sub> Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 1.75\% \text{ @ } 400 - 700\text{nm (N-BK7)}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### Fused Silica with UV-AR Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{abs} \leq 1.0\% \text{ @ } 250 - 425\text{nm}$$

$$R_{avg} \leq 0.75\% \text{ @ } 250 - 425\text{nm}$$

$$R_{avg} \leq 0.5\% \text{ @ } 370 - 420\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### Fused Silica with UV-VIS Coating Typical Transmission



Typical transmission of a 3mm thick fused silica wind with UV-VIS (250-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{abs} \leq 1.0\% \text{ @ } 350 - 450\text{nm}$$

$$R_{avg} \leq 1.5\% \text{ @ } 250 - 700\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### Fused Silica with VIS-EXT Coating Typical Transmission



Typical transmission of a 3mm thick fused silica wind with VIS-EXT (350-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### Fused Silica with VIS-NIR Coating Typical Transmission



Typical transmission of a 3mm thick fused silica wind with VIS-NIR (400-1000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}$$


$$R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}$$

$$R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### Fused Silica with VIS 0° Coating Typical Transmission



Typical transmission of a 3mm thick fused silica wind with VIS 0° (425–675nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.4\% \text{ @ } 425 - 675\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### Fused Silica with YAG-BBAR Coating Typical Transmission



Typical transmission of a 3mm thick fused silica wind with YAG-BBAR (500–1100nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{abs} \leq 0.25\% \text{ @ } 532\text{nm}$$


$$R_{abs} \leq 0.25\% \text{ @ } 1064\text{nm}$$

$$R_{avg} \leq 1.0\% \text{ @ } 500 - 1100\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### Fused Silica with NIR I Coating Typical Transmission



Typical transmission of a 3mm thick fused silica wind with NIR I (600 – 1050nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% \text{ @ } 600 - 1050\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

## Fused Silica with NIR II Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

- $R_{abs} \leq 1.5\%$  @ 750 - 800nm
- $R_{abs} \leq 1.0\%$  @ 800 - 1550nm
- $R_{avg} \leq 0.7\%$  @ 750 - 1550nm

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

## Related Products



Cage System Optical Lens Mounts



C, S, and T-Mount Circular Optic Mounts



PUROSOL™ Optical Cleaner



$\lambda/20$  High Power Laser Line Windows

## Frequently Purchased Together



#15-158 - 550nm CWL, 12.5mm Dia., Hard Coated OD 4.0 50nm Unmounted Bandpass Filter  
C\$259.00

Qty



#15-149 - 650nm CWL, 12.5mm Dia., Hard Coated OD 4.0 25nm Unmounted Bandpass Filter  
C\$259.00

Qty























#13-333 - 12.5mm Dia., 2mm Thick, VIS-EXT Coated,  $\lambda/10$  Fused Silica Windows  
C\$240.80

Qty

## Compatible Mounts

	Title	Type	Compare	Stock Number	Price	Buy
	10.0mm Optic Dia., Optic Mount	Fixed		#64-554	C\$45.85 <a href="#">Request Quote</a>	20+ In Stock <input type="text" value="1"/>

	Title	Type	Compare	Stock Number	Price	Buy
 	5.0 - 25.0mm Optic Height, Metric Bar- Type Optic Holder	Fixed		#55-529	C\$142.80 Request Quote	20+ In Stock <input type="text" value="1"/> 
 	7.0 - 40.0 Optic Height, English Bar- Type Optic Holder	Fixed		#03-676	C\$148.40 Request Quote	20+ In Stock <input type="text" value="1"/> 
 	10.0 - 60.0mm Optic Height, Metric Bar-Type Optic Holder	Fixed		#55-530	C\$151.20 Request Quote	CONTACT US <input type="text" value="1"/> 
 	7.0 - 67.0 Optic Height, English Bar- Type Optic Holder	Fixed		#03-669	C\$162.40 Request Quote	20+ In Stock <input type="text" value="1"/> 
 	8.0 - 118.0 Optic Height, English Bar- Type Optic Holder	Fixed		#03-666	C\$168.00 Request Quote	20+ In Stock <input type="text" value="1"/> 
 	4.0 - 36.0mm Optic Dia., Self-Centering Jaw Clamp	Fixed		#16-077	C\$219.80 Request Quote	5 In Stock <input type="text" value="1"/> 
 	5.0 - 100.0mm Optic Dia., Self-Centering Jaw Clamp	Fixed		#16-078	C\$574.00 Request Quote	CONTACT US <input type="text" value="1"/> 

Check out our full selection of mounts [here](#).

## Resources

### Media Type

- Application Note
- Technical Tool
- Video
- Glossary
- FAQ

APPLICATION NOTE

Anti-Reflection  
(AR) Coatings

APPLICATION NOTE

An  
Introduction to  
Optical  
Coatings

TECHNICAL TOOL

Beam  
Displacement  
Calculator

APPLICATION NOTE

UV vs. IR  
Grade Fused  
Silica

APPLICATION NOTE

Understanding  
Optical  
Windows

VIDEO

Optical  
Windows  
Review

[View More](#)

;