


TECHSPEC<sup>®</sup> 10mm Dia., 1.25mm Thick, YAG-BBAR Coated,  $\lambda$ /10 Fused Silica Window



Stock #13-348 13 In Stock

-

1

+

C\$236<sup>.60</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | C\$236.60 each                |
| Qty 6-25       | C\$189.00 each                |
| Qty 26-49      | C\$176.40 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:Protective Window

Physical & Mechanical Properties

Clear Aperture CA (mm):8.00

Diameter (mm):10.00 +0.00/-0.20

|                      |                             |
|----------------------|-----------------------------|
| 1.25 ±0.10           | Thickness (mm):             |
| +0.00/-0.20          | Dimensional Tolerance (mm): |
| Protective as needed | Bevel:                      |
| 80                   | Clear Aperture (%):         |
| Fine Ground          | Edges:                      |
| <5                   | Parallelism (arcsec):       |
| 0.16                 | Poisson's Ratio:            |
| 73                   | Young's Modulus (GPa):      |

|        |                          |
|--------|--------------------------|
| 522.00 | Knoop Hardness (kg/mm²): |
|--------|--------------------------|

Optical Properties

|                                                                                                              |                                        |
|--------------------------------------------------------------------------------------------------------------|----------------------------------------|
| YAG-BBAR (500-1100nm)                                                                                        | Coating:                               |
| <a href="#">Fused Silica</a> (Corning 7980)                                                                  | Substrate: <div></div>                 |
| 1.458                                                                                                        | Index of Refraction (n <sub>d</sub> ): |
| 20-10                                                                                                        | Surface Quality:                       |
| λ/10                                                                                                         | Transmitted Wavefront, P-V:            |
| 67.8                                                                                                         | Abbe Number (v <sub>d</sub> ):         |
| R <sub>abs</sub> <0.25% @ 532nm<br>R <sub>abs</sub> <0.25% @ 1064nm<br>R <sub>avg</sub> <1.0% @ 500 - 1100nm | Coating Specification:                 |
| 500 - 1100                                                                                                   | Wavelength Range (nm):                 |

|                       |                              |
|-----------------------|------------------------------|
| 5 J/cm² @ 532nm, 10ns | Damage Threshold, By Design: |
|-----------------------|------------------------------|

Material Properties

|                                                                   |                                                              |
|-------------------------------------------------------------------|--------------------------------------------------------------|
| 2.20                                                              | Density (g/cm³):                                             |
| 0.52 (+5 to +35°C)<br>0.57 (0 to +200°C)<br>0.48 (-100 to +200°C) | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |
| 7980 0G                                                           | Fused Silica Grade:                                          |

Regulatory Compliance


|                           |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
| <a href="#">View</a>      | Certificate of Conformance: |
| <a href="#">Compliant</a> | Reach 235:                  |

Product Details






- UV, Visible, and NIR Anti-Reflection Coated Versions Available
- λ/10 Transmitted Wavefront Distortion
- Circular and Square Sizes from 2mm to 150mm
- [1λ](#) or [λ/4](#) UV Fused Silica Windows Also Available




TECHSPEC® λ/10 UV Fused Silica Windows feature laser-grade surface quality and parallelism. In addition, these windows will limit the transmitted wavefront distortion to λ/10. The superior transmission characteristics, excellent thermal properties, and high tolerance manufacturing specifications make these windows an excellent choice for more demanding applications. TECHSPEC λ/10 UV Fused Silica Windows are available for purchase in circular and square sizes ranging from 2mm to 150mm.. These windows are offered uncoated or with anti-reflection coatings optimized for the UV or visible spectrum.

Technical Information



| FUSED SILICA                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |  |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| <div><div>Uncoated Fused Silica<br/>Typical Transmission</div><div>Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra.</div><div><a href="#">Click Here to Download Data</a></div></div>                                                                                                                                                                                                                                                                                                                                                                                                                            |  |
| <div><div>Fused Silica with MgF<sub>2</sub> Coating<br/>Typical Transmission</div><div>Typical transmission of a 3mm thick fused silica window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.</div><div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div><div><math>R_{avg} \leq 1.75\% \text{ @ } 400 - 700\text{nm (N-BK7)}</math></div><div>Data outside this range is not guaranteed and is for reference only.</div><div><a href="#">Click Here to Download Data</a></div></div>                                                                                                         |  |
| <div><div>Fused Silica with UV-AR Coating<br/>Typical Transmission</div><div>Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.</div><div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div><div><math>R_{abs} \leq 1.0\% \text{ @ } 250 - 425\text{nm}</math><br/><math>R_{avg} \leq 0.75\% \text{ @ } 250 - 425\text{nm}</math><br/><math>R_{avg} \leq 0.5\% \text{ @ } 370 - 420\text{nm}</math></div><div>Data outside this range is not guaranteed and is for reference only.</div><div><a href="#">Click Here to Download Data</a></div></div> |  |
| <div><div>Fused Silica with UV-VIS Coating<br/>Typical Transmission</div></div>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |  |

|                                                                                                                                                                       |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                                      | <p>Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 1.0\%</math> @ 350 - 450nm<br/><math>R_{avg} \leq 1.5\%</math> @ 250 - 700nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                   |
| <p><b>Fused Silica with VIS-EXT Coating</b><br/><b>Typical Transmission</b></p>    | <p>Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 0.5\%</math> @ 350 - 700nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                    |
| <p><b>Fused Silica with VIS-NIR Coating</b><br/><b>Typical Transmission</b></p>   | <p>Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 0.25\%</math> @ 880nm<br/><math>R_{avg} \leq 1.25\%</math> @ 400 - 870nm<br/><math>R_{avg} \leq 1.25\%</math> @ 890 - 1000nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p> |
| <p><b>Fused Silica with VIS 0° Coating</b><br/><b>Typical Transmission</b></p>    | <p>Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 0.4\%</math> @ 425 - 675nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                     |
| <p><b>Fused Silica with YAG-BBAR Coating</b><br/><b>Typical Transmission</b></p>  | <p>Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 0.5\%</math> @ 500 - 1100nm</p>                                                                                                                                                                                                                                |

|                                                                                                                                                                           |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                                          | <div><div><math>R_{abs} \leq 0.25\% \text{ @ } 532\text{nm}</math><math>R_{abs} \leq 0.25\% \text{ @ } 1064\text{nm}</math><math>R_{avg} \leq 1.0\% \text{ @ } 500 - 1100\text{nm}</math></div><div>Data outside this range is not guaranteed and is for reference only.</div><div><a href="#">Click Here to Download Data</a></div></div>                                                                                                                                                                                                                                             |
| <div><div>Fused Silica with NIR I Coating</div><div>Typical Transmission</div></div>   | <div><div>Typical transmission of a 3mm thick fused silica window with NIR I (600 - 1050nm) coating at 0° AOI.</div><div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div><div><math>R_{avg} \leq 0.5\% \text{ @ } 600 - 1050\text{nm}</math></div><div>Data outside this range is not guaranteed and is for reference only.</div><div><a href="#">Click Here to Download Data</a></div></div>                                                                                                                             |
| <div><div>Fused Silica with NIR II Coating</div><div>Typical Transmission</div></div> | <div><div>Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI.</div><div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div><div><math>R_{abs} \leq 1.5\% \text{ @ } 750 - 800\text{nm}</math><math>R_{abs} \leq 1.0\% \text{ @ } 800 - 1550\text{nm}</math><math>R_{avg} \leq 0.7\% \text{ @ } 750 - 1550\text{nm}</math></div><div>Data outside this range is not guaranteed and is for reference only.</div><div><a href="#">Click Here to Download Data</a></div></div> |

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts