

1.0mm Dia, 810nm DWL, 0.0mm WD, Uncoated, GRIN Lens



Stock **#64-523** ☐ In Stock

-

1

+

C\$80.50

ADD TO CART

Qty 1-10
C\$80.50
Qty 11+
C\$71.40
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm): 1.00 +0.00/-0.01
Effective Focal Length EFL (mm): 0.93
Substrate: ☐ Aluminosilicate Glass Embedded with Silver Ions
f#: 0.93

Numerical Aperture NA: 0.54
Coating: Uncoated
Type: Gradient Index Lens
Wavelength Range (nm): 400 - 1600
Clear Aperture (%): 90.00
Focal Length Specification Wavelength (nm): 810.00
Gradient Constant (mm⁻¹): 0.660
Index of Refraction n_d - Center of Lens: 1.624
Length (mm): 2.38
Pitch: 0.25
Surface Quality: 40-20
Working Distance (mm): 0
Working Distance Tolerance (mm): ±0.01
Length Tolerance (%): ±5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View