


10mm Dia x 10mm Focal Length, Spherical Mirror



Stock **#46-231** ☐ In Stock

1

C\$52.50

ADD TO CART

Qty 1-49

C\$52.50

Qty 50+

C\$46.90

Volume Pricing

[Request Quote](#)

Get Product Downloads

Substrate: ☐
[N-BK7](#)

Focal Length Tolerance (%):
±2

Surface Quality:
60-40

Surface Accuracy:
λ/4

Diameter (mm): 10.00 +0.00/-0.30
Effective Focal Length EFL (mm): 10.00
Radius of Curvature (mm): 20.00
Aperture (f/#): f/1
Coating: Protected Aluminum (400-2000nm)
Coating Specification: R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm
Coating Type: Metal
Back Surface: Ground
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.30
Edge Thickness ET (mm): 3.63
Edges: Ground
Radius R (mm): 20.0
Type: Spherical Mirror
Wavelength Range (nm): 400 - 2000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant