

TECHSPEC® 10mm Dia. x 15mm FL, VIS-NIR Inked, Double-Convex Lens



Stock **#63-664-INK** 3-5 DAYS

[Other Coating Options](#)

- 1 +

C\$74.20

ADD TO CART

Qty 1-9
C\$74.20
Qty 10+
C\$66.85
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
10.00 ±0.025

Back Focal Length BFL (mm):
13.80

Effective Focal Length EFL (mm): 15.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R_{abs} ≤0.25% @ 880nm R_{avg} ≤1.25% @ 400 - 870 nm R_{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.77
Radius R₁–R₂ (mm): 14.88
Clear Aperture CA (mm): 9.00
f/#: 1.5
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.33
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View