

10mm Dia. x 6.6mm FL, MgF₂ Molded Aspheric Condenser Lens



Molded Aspheric Condenser Lenses

Stock **#35-038** ☐ **In Stock**

[Other Coating Options](#)

1

C\$59.50

ADD TO CART

Qty 1-10

C\$59.50

Qty 11+

C\$52.22

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
10.00 +/-0.3

Effective Focal Length EFL (mm):
6.60 @ 587.6nm

Numerical Aperture NA:
0.76

Back Focal Length BFL (mm): 3.30 +/-0.25
Substrate:  Liba2000+
Focal Length Tolerance (%): ±7
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Centering (arcmin): ≤30
Surface Quality: 5/3 x0.4; E 0.2
Clear Aperture CA (mm): 8.00
Edge Thickness ET (mm): 0.46
Center Thickness CT (mm): 5.00 ±0.20
f/#: 0.66
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 10.0
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 400 - 700
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant