

[See all 8 Products in Family](#)

TECHSPEC[®]

1.0mm Diameter, N-BK7 Half-Ball Lens



TECHSPEC[®] N-BK7 Half-Ball Lenses

Stock **#49-568** 20+ In Stock

-

1

+

C\$80⁵⁰

ADD TO CART

Volume Pricing	
Qty 1-10	C\$80.50 each
Qty 11-49	C\$72.10 each
Need More?	Request Quote

Product Downloads

General

Half-Ball Lens

Type:

Physical & Mechanical Properties

1.00

Diameter (mm):

±0.05

Center Thickness Tolerance (mm):

Radius R (mm):

0.50	
	Radius Tolerance (μm):
+0.0/-1.5	

	Thickness (mm):
0.50	

	Diameter Tolerance (μm):
±2.5	

Optical Properties

	Substrate: ☐
N-BK7	
	Coating:
Uncoated	

	Wavelength Range (nm):
350 - 2200	

Regulatory Compliance

	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	

	Reach 247:
Compliant	

Product Details

- Fiber Coupling Half-Spheres
- Collimating Lenses

TECHSPEC® N-BK7 Half-Ball Lenses are ideal for applications such as fiber communication, endoscopy, microscopy, optical pick-up devices, and laser measurement systems. Half-ball (hemispherical) lenses can be interchanged with full ball lenses if the physical constraints of an application require a more compact design. These collimating lenses are uncoated, with a wavelength range of 350-2200nm. TECHSPEC® N-BK7 Half-Ball Lenses are offered in diameters ranging from 0.50 to 10.00mm.

Technical Information

