

TECHSPEC[®] 10mm Schmidt-Pechan Prism



TECHSPEC[®] Pechan Prism

Stock **#36-038** 3 In Stock

-

1

+

C\$609⁹²

ADD TO CART

Volume Pricing	
Qty 1-5	C\$609.92 each
Qty 6-25	C\$488.24 each
Qty 26-99	C\$457.07 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Schmidt-Pechan Prism

Type:

Physical & Mechanical Properties


20.2	Height (mm):
12.99	Thickness (mm):
±0.1	Dimensional Tolerance (mm):
14.00	Width (mm):
Optical Properties	
MS 0° & Aluminized	Coating:
N-BK7	Substrate: □
40-20	Surface Quality:
Right-Handed	Image Orientation:
Coating Specification: Entrance/Exit Faces: R _{avg} ≤0.4% @ 425 - 675nm Roof: R _{avg} >85% @ 400 - 700nm w/Black Overpaint	
0	Ray Deviation (°):
400 - 700	Wavelength Range (nm):
±10	Ray Deviation Tolerance (arcmin):
1.00	Power (fringes) @ 632.8nm:
0.25	Irregularity (fringes) @ 632.8nm:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS


- Provides Inline Image Rotation of 180°
- Compact Design for OEM Integration
- Air Spaced for Optimal Performance

TECHSPEC® Schmidt-Pechan Prisms leverage Edmund Optics' manufacturing expertise to deliver a precision inline instrumentation prism to rotate an image by 180 degrees. This image rotation is employed in many direct view applications and replaces a relay prism or lens system for a more compact optical train. Overall clarity of the system is ensured by adding both an anti-reflective and metallic coating to each prism. The TECHSPEC® Schmidt-Pechan Prisms feature 5 arcsecond roof angle tolerances to maintain image resolution.


TECHNICAL INFORMATION



#36-038



Schmidt-Pechan Prism Ray Path



Schmidt-Pechan Prism Tunnel Diagram