

TECHSPEC® 10X, 266nm Vega® Nd:YAG Laser Line Beam Expander



TECHSPEC® Vega™ Laser Line Beam Expanders



Stock **#35-114** ☐ In Stock

-

1

+

C\$693.00

ADD TO CART

Qty 1-9

C\$693.00

Qty 10+

C\$610.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):
0

Coating:
Laser V-Coat (266nm)

Design Wavelength DWL (nm): 266
Entrance Aperture (mm): 7.5
Exit Aperture (mm): 32
Expansion Power: 10X
Substrate: Fused Silica (Corning 7980)
Length (mm): 85.40
Mounting Threads: Input: Male M30 x 1 Output: Female M42 x 0.5 (not intended for use)
Transmission (%): >97 (nominal)
Type: Beam Expander
Weight (g): 258
Housing Diameter (mm): 48
Transmitted Wavefront, P-V: <λ/10 for 2.2mm input beam (nominal, λ = DWL)
Coating Specification: R_{abs} <0.25% @ 266nm
Wavelength Range (nm): 250 - 280
Style: Fixed Magnification
Damage Threshold, By Design: 1.5 J/cm² @ 266nm, 10ns, 20Hz
Divergence Adjustment: Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View