

TECHSPEC[®] 10mm NIR I Hypotenuse, BBAR Right Angle Prism



Broadband Anti-Reflection Coated Hypotenuse Prism

Stock #34-407 10 In Stock

-

1

+

C\$161⁷⁶

ADD TO CART

Volume Pricing	
Qty 1-5	C\$161.76 each
Qty 6-25	C\$129.85 each
Qty 26-49	C\$121.69 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Right Angle Prism

Type:

Physical & Mechanical Properties


Dimensional Tolerance (mm):	
+0/-0.1	
Bevel:	
Protective as needed	
Length of Hypotenuse (mm):	
14.10	
Length of Legs (mm):	
10.00	
Optical Properties	
Beam Deviation (arcsec):	
±15	
Coating:	
NIR I (600-1050nm)	
Substrate: ☐	
N-BK7	
Surface Quality:	
40-20	
Image Orientation:	
Left-Handed	
Ray Deviation (°):	
90	
Wavelength Range (nm):	
350 - 2200	
Power (fringes) @ 632.8nm:	
1.25	
Irregularity (fringes) @ 632.8nm:	
0.25	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 235:	
Compliant	




PRODUCT DETAILS

- Single Axis Retroreflector
- Right-Handed Image
- VS and NIR Options Available


TECHSPEC® BBAR (Broadband Anti-Reflection) Coated Hypotenuse Right Angle Prisms are ideal for applications that require a single axis retroreflector. These prisms feature coating options that cover the visible and near-infrared spectrum, as well as tight angular tolerances. These TECHSPEC® BBAR Coated Hypotenuse Right Angle Prisms are also available in custom sizes.

TECHNICAL INFORMATION







Right Angle Prism Ray Path



Right Angle Prism Ray Path



Right Angle Prism Tunnel Diagram



Right Angle Prism Tunnel Diagram

CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).