

[See all 10 Products in Family](#)

**TECHSPEC® 1:1 with 35mm and 35mm EFL Achromats, NIR Achromatic Pair**



TECHSPEC Mounted Near-IR (NIR) Achromatic Lens Pairs

Stock **#47-293** [CONTACT US](#)

⊖ 1 ⊕ C\$383<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	C\$383.60 each
Qty 6-25	C\$306.60 each
Qty 26-49	C\$296.80 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Relay Lens Type:

**Physical & Mechanical Properties**

22.0 Clear Aperture CA (mm):

1.38 Center Air Spacing (mm):

30.0 +0.0/-0.10 **Housing Diameter (mm):**

34.00 ±0.2 **Housing Length (mm):**

25.00 **Image Distance (mm):**

**Construction:**  
Achromat Pair in Anodized Aluminum Housing

## Optical Properties

**Substrate:**   
N-LAK22 / N-SF6 / N-LAK22 / N-SF6

40-20 **Surface Quality:**

f/1.55 **Working f#:**

NIR II (750-1550nm) **Coating:**

**Coating Specification:**  
 $R_{abs} \leq 1.5\% @ 750 - 800nm$   
 $R_{abs} \leq 1.0\% @ 800 - 1550nm$   
 $R_{avg} \leq 0.7\% @ 750 - 1550nm$

35.00 **Effective Focal Length EFL A (mm):**

35.00 **Effective Focal Length EFL B (mm):**

1:1 **Magnification:**

25.00 **Object Distance (mm):**

750 - 1550 **Wavelength Range (nm):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- 30mm Diameter Package Designed for NIR Applications
- Optimized for Various Magnification Ratios
- Ideal for Integration into OEM Applications
- NIR II Coated for 750-1550nm

Our 15.0mm and 30.0mm Mounted Achromatic Pairs combine our popular TECHSPEC® achromats into common configurations used for relay and projection applications. Packaged in a slim-line aluminum housing, each pair is ready for integration into a host of OEM applications, eliminating the need to handle loose optics. Each lens has also been oriented for optimum system performance. All lenses AR coated. Lower f# pairs may not be ideal for imaging applications depending on the performance requirements. Cylinder lenses can be incorporated into empty barrels in order to generate lines or sheets of light.

## Technical Information

