

TECHSPEC® 1:1 with 75mm and 75mm EFL Achromats, NIR Achromatic Pair



TECHSPEC Mounted Near-IR (NIR) Achromatic Lens Pairs

Stock **#47-300** [CONTACT US](#)

- 1 +

C\$326.20

ADD TO CART

Qty 1-5

C\$326.20

Qty 6+

C\$261.10

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture CA (mm):
22.0

Center Air Spacing (mm):
4.66

Substrate: [N-LAK22](#) / [N-SF6](#) / [N-LAK22](#) / [N-SF6](#)

Surface Quality:

40-20
Working f#: f/3.40
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Effective Focal Length EFL A (mm): 75.00
Effective Focal Length EFL B (mm): 75.00
Housing Diameter (mm): 30.0 +0.0/-0.10
Housing Length (mm): 34.00 ±0.2
Magnification: 1:1
Object Distance (mm): 64.24
Image Distance (mm): 64.24
Construction: Achromat Pair in Anodized Aluminum Housing
Type: Relay Lens
Wavelength Range (nm): 750 - 1550

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View