

[See all 2 Products in Family](#)

## 1/2" CCD NIR (1460-1600nm) Analog Camera, EIA



1460-1600nm Near-Infrared Camera (Front)



Stock #56-567 **4 In Stock**

⊖ 1 ⊕ C\$3,717<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	C\$3,717.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

NIR **Spectrum:**

### General

NIR Camera **Type:**

Scintacor **Manufacturer:**

### Physical & Mechanical Properties

**Dimensions (mm):**  
64.6 x 34 x 37 (includes connectors and lens mount)

**Weight (g):**  
90

**Housing:**  
Full

## Sensor

**Sensor Format:**  
1/2"

**Resolution (Megapixels):**  
0.30

**Pixels (H x V):**  
768 x 494

**Pixel Size, H x V (µm):**  
8.4 x 9.8

**Sensing Area, H x V (mm):**  
6.4 x 4.8

**Type of Sensor:**  
Interlaced CCD

**Exposure Time:**  
1/60 - 1/100,000s

**Dynamic Range (dB):**  
Not Specified

**Signal Format:**  
EIA

## Electrical

**Power Consumption (W):**  
Not Specified

## Hardware & Interface Connectivity

**Interface:**  
Analog

**Connector:**  
Analog, BNC

**Power Supply:**  
Separate Power Supply (Included)

**GPIOs:**  
N/A

**Synchronization:**  
Internal

**Interface Port Orientation:**  
Back Panel

**GPIO Connector Type:**  
None

**Power Requirement:**  
12 VDC, 160 mA

## Threading & Mounting

**Mount:**  
C-Mount

**Mounting Threads:**  
1/4-20 (Integrated into Housing)

## Environmental & Durability Factors

**Operating Temperature (°C):**  
-10 to +40

**Storage Temperature (°C):**  
Not Specified

## Regulatory Compliance

**Reach 191:**  
[Compliant](#)

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

## Product Details

- Low Cost
- Compact Size

- Standard Analog Video Output
- High Speed Electronic Shutter

This near IR camera utilizes a high resolution CCD array that has been specially treated with a phosphor coating. The result is a camera that has an effective response between 1460nm to 1600nm at a cost much lower than seen with other detector technologies. The high-speed electronic shutter allows for easy attenuation of high-level signals often associated with laser applications. Features a maximum CW power saturation of 100mW/cm<sup>2</sup> at 1550nm. The camera is ideal for applications including laser alignment, telecommunication testing, as well as inspection. While standard CCD lenses can be utilized in the near IR, their optical designs and coating are generally not optimized for this region of the spectrum. We recommend video lenses designed specifically for the near IR region.

---