

10X Focusing Lens



10X Focusing Lens



Stock **#28-779** **5 In Stock**

-

1

+

C\$553⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$553.00 each
Need More?	Request Quote

Product Downloads

General

Note:
Use with #15-943 instead of #18-509 for uniform in-line illumination.

Physical & Mechanical Properties

104.23	Length (mm):
35.00	Maximum Diameter (mm):

Threading & Mounting

	Mounting Threads:
M29 x0.75	

Regulatory Compliance


	Certificate of Conformance:
View	

Product Details

- Up to 43% Smaller than Industry Standard Systems
 - Optimized Performance up to 1.1" Sensor
 - Ideal for Life Science and Industrial Applications
 - Winner of the [2023 Bronze VSD Innovators Award](#)
- Edmund Optics® 120i Plan APO Infinity Corrected Objectives are infinite conjugate microscope objectives that offer exception image flatness and chromatic correction over 400-700nm. These objectives were designed for a 1.1" sensor to offer a large field of view and reliable image quality for high-throughput imaging applications. Ideal for life science and machine vision applications such as microscopy, flow cytometry, pharmaceutical inspection, and assembly line or fault inspection.
- These objectives won the [2023 Bronze VSD Innovators Award](#).

Technical Information

Compact Tube Lens System



Standard Tube Lens System

