

# 1200 Grooves/mm, 30mm Square, VIS Holographic Grating



Reflective Holographic Gratings

Stock **#55-264** ☐ In Stock

-

1

+

C\$315.00

ADD TO CART

Qty 1+

C\$315.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Groove Density (grooves/mm):  
1200

Wavelength Range (nm):  
400 - 700

Dimensions (mm):  
30.0 x 30.0 ±0.5

Coating:  
Bare Aluminum

|                                                                                                                    |
|--------------------------------------------------------------------------------------------------------------------|
| <b>Construction:</b><br>Holographic Grating                                                                        |
| <b>Length (mm):</b><br>30.00                                                                                       |
| <b>Substrate:</b> <br>Float Glass |
| <b>Thickness (mm):</b><br>9.50 ±0.5                                                                                |
| <b>Type:</b><br>Reflective Diffraction Grating                                                                     |
| <b>Wavelength:</b><br>VIS                                                                                          |
| <b>Width (mm):</b><br>30.00                                                                                        |
| <b>Alignment of Grooves to Edge (°):</b><br>±0.5                                                                   |
| <b>Absolute Peak Efficiency, Typical (%):</b><br>73                                                                |
| <b>Peak Efficiency Avg, Typical (%):</b><br>>63                                                                    |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---